



Grundgestell, mit 22/32/42HE

- Grundausrüstung:** Grundgestell
4x Lochrasterprofile 19" (Vorder-/Rückseite)
40x Käfigmuttern mit Schrauben
4x Nivelier Füße
4x Räder (2x mit / 2x ohne Feststeller)
- Farbe:** Lichtgrau RAL7035
- Besonderheiten:** Grundgestell zerlegt (Aufbauzeit ca.20min)
19" Lochrasterprofile verstellbar
Es können entweder die Nivelier Füße montiert werden oder die Räder
- 19" Profilabstand:** veränderbar in 40mm Schritten
- Belastbar:** bis max.400Kg



Artikel	Außenmaße (B/T/H)	Nutzhöhe	Farbe	Herstellernr.	19" Profilabstand
156698	600/600/674	12HE	Lichtgrau RAL7035	ALL-SRB6612Grau	245-405 mm
126001	600/600/1120	22HE	Lichtgrau RAL7035	ALL-SRB6622Grau	245-405 mm
126000	600/600/1566	32HE	Lichtgrau RAL7035	ALL-SRB6632Grau	245-405 mm
125999	600/600/2011	42HE	Lichtgrau RAL7035	ALL-SRB6642Grau	245-405 mm
156699	600/1000/674	12HE	Lichtgrau RAL7035	ALL-SRB6112Grau	405-805 mm
125998	600/1000/1120	22HE	Lichtgrau RAL7035	ALL-SRB6122Grau	405-805 mm
125997	600/1000/1566	32HE	Lichtgrau RAL7035	ALL-SRB6132Grau	405-805 mm
125996	600/1000/2011	42HE	Lichtgrau RAL7035	ALL-SRB6142Grau	405-805 mm
139266	600/1200/1120	22HE	Lichtgrau RAL7035	ALL-SRB61222Grau	405-1080 mm
139267	600/1200/1566	32HE	Lichtgrau RAL7035	ALL-SRB61232Grau	405-1080 mm
139269	600/1200/2011	42HE	Lichtgrau RAL7035	ALL-SRB61242Grau	405-1080 mm




Seitenansicht




19" Profil detailansicht



Profilabstand veränderbar




Step 3: Assembly the frame and plinth by 16 sets M6*12 screws and M6 flange nuts.



Step 4: Assembly the top connection part on the frames by 8 sets M6*12 screws and M6 flange nuts.

Note: After assembly, please adjust the diagonal size of the cabinet to ensure homogeneous space for all doors and all doors work well.

4-POST Open Frame Rack Assembly Instruction



Packaging List

1. Vertical rail - 4pcs
2. Horizontal beam - 4pcs
3. Plinth - 2pcs
4. 2" heavy-duty castor (2 pcs with brake) - 4pcs
5. Top connection part - 2pcs
6. Levelling feet - 4pcs

Item List of Accessories Packaging

Assembly Hardwares Kits:








- M6*12 screw - 72pcs
- M6 Flange nut - 72pcs
- 2" heavy-duty castor -2pcs
- 2" heavy-duty castor with brake -2pcs
- Levelling feet - 4pcs
- M12 flange nut - 4pcs

End User Hardwares Kits:


U Capacity $\leq 27U$, 20 sets cagenuts ; $27U < U$ Capacity $\leq 37U$, 30sets cagenuts ; U Capacity $> 37U$, 40 sets cagenuts.
(cagenut : M6*12 screw & M6 cage nut)

Tips: Check the quantities of the items before assembly


Diagram of accessories

NO.	FIGURE	DESCRIPTION
1		M6 flange nut
2		M6*12 Screw
3		2" heavy-duty castor
4		2" heavy-duty castor with brake
5		Levelling feet
6		M6 cage nut
7		M12 flange nut

Installation



Step 1: Assembly vertical rails and horizontal beams to form the frame with 32 sets M6*12 screws and M6 flange nuts.



Step 2: Assembly the castors on the Plinths by 16 sets M6*12 screws and M6 flange nuts, or assembly the levelling feet, with M12 flange nuts.